

SIMPLEX sledge hammers • TPE-soft / rubber composition; with cast iron housing and Hickory handle EH 3012.



Product Description

The SIMPLEX series 3012 is available with the popular insert combination of TPE-soft / rubber composition. The blue TPE-soft insert (series 3201) is the softest insert of the SIMPLEX line and offers strong impact cushioning for work requiring a light touch. Unlike conventional rubber mallets, it does not leave behind any undesired black marring.

Ultra low-wear, impact cushioning and odourless, the medium hard rubber insert (series 3202) offers a much longer service life than a conventional rubber hammer.

Made of cast iron, the housing comes with an integrated handle protection sleeve that provides for a high level of break resistance.

The long-fibre and ultra durable hickory handle is varnished and shaped ergonomically.

In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources.

Measuring 3,205g, and 80cm in total weight and total length, respectively, this sledge hammer is available in D80mm and as a sledge hammer including rubber insert with "stand-up" (3012.281).

Product features:

- SIMPLEX soft-face mallet with the insert combination of TPE-soft (blue, soft, no marring) / rubber composition (black, medium hard, impact cushioning, odourless, low-wear).
- Cast iron housing with integrated handle protection sleeve and excellent break resistance.
- High-quality, vibration-damping, and ergonomically shaped wooden handle; grip area with double coat of varnish (resistant to dirt).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in D80mm (3,205g total weight) and as a sledge hammer including rubber insert with "stand-up" (3012.281).

Application Areas

Gardening and landscaping, curbstone setting, masonry and stairs setting, fence construction, scaffold construction, tent construction, prefabricated house construction

Material

Handle

- Hickory

insert 1

- TPE-soft, blue
- Non-marring
- Soft

insert 2

- Rubber composition, black
- Medium hard
- impact cushioning
- Odorless

Housing

- Cast iron

Order information

Ø	Dimensions		Length x Width x Height [mm]	[g]	GTIN	profiel@ss 5.0	ecl@ss 10.1	Art. No.
80	175	800	800 x 175 x 80	3205	4030618312352	AAA938c002	21-04-09-20	3012.081

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.