

## Spannhebel EH 24430.



### Produktbeschreibung

#### Werkstoff


##### Hebel

- Stahl, brüniert
- Rostfreier Stahl 1.4305, matt gestrahlt

##### Kugelknopf

- Duroplast PF 31, schwarz, DIN 319


### Maßzeichnung



### Bestellinformationen

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub> H7	d <sub>4</sub>	Abmessungen				t <sub>1</sub>	t <sub>2</sub>	[g]	Art.-Nr.
				d <sub>5</sub>	h	l	[mm]				
<b>mit Innengewinde – Bild 1, Stahl</b>											
20	M 8	–	8	20	33	67	15	–	97	24430.0022	
22	M10	–	8	20	37	85	15	–	115	24430.0032	
25	M12	–	10	25	42	95	18	–	165	24430.0038	
28	M12	–	12	30	47	108	18	–	262	24430.0042	
32	M16	–	12	32	52	126	23	–	354	24430.0048	
36	M16	–	14	35	58	138	24	–	519	24430.0052	
40	M20	–	16	40	64	154	27	–	708	24430.0058	
<b>mit glatter Bohrung – Bild 2, Stahl</b>											
20	–	10	8	20	33	67	–	16	85	24430.0020	
22	–	10	8	20	37	85	–	19	113	24430.0030	
25	–	12	10	25	42	95	–	21	170	24430.0035	
28	–	12	12	30	47	108	–	23	268	24430.0040	
32	–	16	12	32	52	126	–	28	351	24430.0045	
36	–	16	14	35	58	138	–	28	524	24430.0050	
40	–	20	16	40	64	154	–	30	706	24430.0055	
<b>mit Innengewinde – Bild 1, Rostfreier Stahl</b>											
22	M 8	–	8	20	37	85	15	–	121	24430.0230	
25	M10	–	10	25	42	95	18	–	186	24430.0236	
28	M12	–	12	30	47	108	18	–	262	24430.0242	
32	M16	–	12	32	52	126	23	–	354	24430.0248	

## Anwendungsbeispiel



## Compliance

Für detaillierte Compliance Informationen wählen Sie bitte die gewünschte Artikelnummer.