

Drop-mallets/Punches kit • 4 pcs.

EH 3408.



产品描述

These little helpers made by Halder are packaged in a 4 pcs. box set. The high-quality plastic case ensures that the products are easy to store and carry along. The punches and drop-mallets are fitted on both ends with replaceable, very wear-resistant and splinter-proof heads made of special nylon (art. no. 3508.010 / .015 / .020 / .030). They thus allow for secure and gentle work with a steel hammer.

Besides, drop-mallets are, in effect, soft-face mallets without a handle, allowing the user to hold the hammer head directly in the hand. Suitable for use in situations where limited accessibility makes it impossible to work with a mallet, they are also ideal for applying exactly the amount of impact force that is needed for striking the workpiece with perfect precision and for working with minimum force. The drop-mallets offer non-rebound comfort thanks to their steel shot filling. The resulting effect is that the energy of the steel shot is transferred with a slight delay when the mallet's contact surface hits the workpiece. The reduced rebound lets the impact energy be absorbed with perfect efficiency, allowing for work with reduced strain on the joints and low noise. The drop-mallets make work much less strenuous - especially in environments with limited accessibility, e.g. during assembly, repair and maintenance, and during work that calls for a well-dosed application of impact force.

Product features:


- 4 pcs. bonus box set consisting of two drop-mallets and two punches.
- Premium, long-lasting plastic case for easy carrying.
- Punches with diameters of 10mm and 15mm (art. no. 3408.010 / 3408.015).
- Drop-mallets with diameters of 20 mm and 30 mm (art. no. 3408.020 / 3408.030).
- Replaceable, very wear-resistant and splinter-proof heads made of special nylon fitted on both ends.
- Allow for secure, gentle and noise-dampening work with a steel hammer.
- The drop-mallets are also non-rebound.
- Allow for an exact application of the impact force.
- The solution for work in areas with limited accessibility.

材质

入子

- 尼龙，白色
- 中高硬度锤击
- 非常耐磨
- 无碎屑 (即使温度低于0)
- 油和油脂抗性

订单信息

尺寸 长 x 宽 x 高 [mm]	 [g]	GTIN	proficl@ss 5.0	ecl@ss 10.1	品号
230 x 45 x 180	1220	4030618312109	AAA905c002	21-04-09-16	3408s005

遵守

含铅 - 符合例外 6a / 6b / 6c

含有 >0.1% w/w 的 SVHC 物质

含铅 - SVHC [REACH] 清单截至 2024 年 1 月 23 日

包含 65 号提案的物质



铅暴露会导致癌症和生殖伤害

<https://www.P65Warnings.ca.gov/>

不含冲突矿物

„本产品不含来自刚果民主共和国或邻近国家的任何被指定为“冲突矿物”的物质，例如钽、锡、金或钨。