

## FIELDS OF APPLICATION

### CONSTRUCTION/GARDENING/LANDSCAPING

→ **Floor tiling, paving (sensitive material)**  
3113 SIMPLEX soft-face mallet · TPE-soft/TPE-mid · Ø 30-60 mm

→ **Curbstone setting, paving, formwork construction**  
3027 SIMPLEX soft-face mallet · rubber comp./superplastic · Ø 30-80 mm

→ **Curbstone setting, bracket stone setting**  
3027 SIMPLEX soft-face mallet · rubber comp./superplastic · Ø 80-100 mm

→ **Natural stone setting masonry-/stairs setting**  
3013 SIMPLEX soft-face mallet · TPE-soft/TPE-mid · Ø 30-60 mm

→ **Concrete formwork**  
3366 SUPERCRAFT sledge hammer, non-rebound · Ø 80-100 mm

### MAINTENANCE/REPAIR

→ **Mild to moderate work**  
3968 BASEPLEX soft-face mallet · cellulose acetate/nylon · Ø 25-50 mm

3026 SIMPLEX soft-face mallet · rubber comp./plastic · Ø 30-60 mm

→ **Powerful work**  
3366 SUPERCRAFT soft-face mallet, non-rebound · Hickory handle · Ø 20-80 mm

3389 SUPERCRAFT soft-face mallet, non-rebound · 3-comp.-handle · Ø 40-60 mm

3666 MAXXCRAFT locksmith's hammer · 300-1.000 g

→ **Automotive and truck sector**  
3029 SIMPLEX soft-face mallet · rubber comp./soft metal · Ø 30-80 mm

3749 SIMPLEX soft-face mallet · copper/soft metal · Ø 30-40 mm

3389 SUPERCRAFT soft-face mallet, non-rebound · 3-comp.-handle · Ø 40-60 mm

3408 Punch · Ø 10-15 mm

→ **Changing stucked tires**  
3379 BLACKCRAFT soft-face mallet, non-rebound · Ø 40-60 mm

### JOINERY/CARPENTRY

→ **Setting light/sensitive workpieces, veneering, furniture assembly**  
3117 SIMPLEX soft-face mallet · TPE-soft/superplastic · 50x40 · Ø 50 mm

→ **Window and door construction**  
3380 SECURAL soft-face mallet, non-rebound · 30x40 mm · 35x45 mm

→ **Pin driving**  
3666 MAXXCRAFT locksmith's hammer · 300-1.000 g

→ **Roof setting**  
3366 SUPERCRAFT sledge hammer, non-rebound · Ø 80-100 mm

### INTERIOR WORK

→ **Parquet and laminate flooring**  
3380 SECURAL soft-face mallet, non-rebound · 30x40 mm · 35x45 mm

3666 MAXXCRAFT locksmith's hammer · 300-1.000 g

→ **Floor tiling**  
3113 SIMPLEX soft-face mallet · TPE-soft/TPE-mid · Ø 30-60 mm

→ **Drywall construction**  
3013 SIMPLEX soft-face mallet · TPE-soft/TPE-mid · Ø 30-60 mm

→ **Install ceiling moldings**  
3408 Drop-mallet, non-rebound · Ø 20-50 mm

### SHEET METAL FORMING

→ **Folding and bending work**  
3366 SUPERCRAFT soft-face mallet, non-rebound · Hickory handle · Ø 20-80 mm

3380 SECURAL soft-face mallet, non-rebound · 30x40 mm · 35x45 mm

3968 BASEPLEX soft-face mallet · cellulose acetate/nylon · Ø 25-50 mm

→ **Installation work**  
3380 SECURAL soft-face mallet, non-rebound · 30x40 mm · 35x45 mm

3906 BASEPLEX soft-face mallet · cellulose acetate · Ø 25-50 mm

3677 FERROPLEX combi hammer · Ø 30-35 mm

### METALWORKING INDUSTRY

→ **Positioning and adjusting of workpieces**  
3386 SUPERCRAFT soft-face mallet, non-rebound · Hickory handle · Ø 20-80 mm

3377 SUPERCRAFT soft-face mallet, non-rebound · Steel tube handle · Ø 25-70 mm

3380 SECURAL soft-face mallet, non-rebound · 30x40 mm · 35x45 mm

3028 SIMPLEX soft-face mallet · nylon/rubber comp. · Ø 30-80 mm

3408 Drop-mallet, non-rebound · Ø 20-50 mm

→ **Straightening work, plant construction**  
3748 SIMPLEX soft-face mallet · copper/nylon · Ø 30-40 mm

3666 MAXXCRAFT locksmith's hammer · 300-1.000 g

→ **Housing assembly, mould construction**  
3089 SIMPLEX soft-face mallet · nylon/soft metal · Ø 30-80 mm

### AGRICULTURE/FORESTRY

→ **Fence construction**  
3007 SIMPLEX sledge hammer · superplastic · Ø 80-140 mm

3386 SUPERCRAFT sledge hammer, non-rebound · Ø 80-100 mm

→ **Splitting 1-metre logs, wedge work**  
3007 SIMPLEX splitting maul · 4.100 g

→ **Splitting of coniferous wood, wedge work**  
3007 SIMPLEX splitting axe · 2.700 g

→ **Splitting of hardwood, wedge work**  
3007 SIMPLEX splitting axe with wedge bars · 2.840 g

→ **Splitting 1-metre logs**  
3556 Halder twisted splitting wedge

→ **Splitting of smaller logs/kindling**  
3555 Halder hand axe · forged