# V-Block Elements right/left 1648.700





# **Product Description**

#### **Material**

• Steel, case-hardened, ground

# **Drawing**





ø-Area	Distance	X
40-330	1x50= 50	190
140-430	2×50=100	240
240-530	3x50=150	290
340-630	4×50=200	340
440-730	5x50=250	390
540-830	6x50=300	440
640-930	7x50=350	490
740-1030	8x50=400	540
840-1130	9x50=450	590

Erwin Halder KG

## **Order information**

System	Dimensions				ı	Art. No.			
	b <sub>1</sub>	d <sub>1</sub>	s	а	_				
		[m	[g]						
right – picture 2									
L16	53	16	20	17	1437	1648.700			



www.halder.com Page 1 of 2 Published on: 3.2.2024

### Compliance

### **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2

Published on: 3.2.2024