Spring Bodies 22100.0052

DUDUN

Product Description

Spring bodies can be used for locating.

Material

Body

· Steel, nickel-plated

Spring

Stainless steel 1.4310


More information

Notes

DA D

Special springs on request.

Drawing




picture 1

Order information

Dimensions					Stroke	Spring load ¹⁾		Spring rate	<u>.</u>	Ĭ	Art. No.
d1	Lo	L ₀ L		L ₃	L ₃ S	F1	F ₂		max.		
±0.05		for F₁	for F ₂			~	~				
[mm]					[mm]		[N]	[N/mm]	[°C]	[g]	
body from steel, round – picture 1											
5	16	13	10.4	8	2.6	8	15	2.7	250	0.6	22100.0052

1) statistical average value

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.