Clamping Pins • self-locking, with span compensation 22360.0022



Product Description

Used for fixing and simultaneously tightly connecting thin walled plates. Clamping distance of 5 mm for clamping of sheets for welding work, for protection, coverings, to close doors etc. All versions are corrosion resistant. Version with ergonomic grip.

Material

Pin partStainless steel 1.4305

Handle

• Thermoplastic PA 6, grey

Spring

Stainless steel

Operation

The balls are unlocked by pressing the button.

More information


Accessories


Can easily be fitted with retaining cable EH 22400.

Further products

- Locating Bushings, for ball lock pins and socket pins
- Locating Bushings, with flange, for ball lock pins and socket pins
- Retaining Cables

Drawing






Order information

Dimensions									Location hole H11	Clamping force			Ĭ	Art. No.
d ₁ -0.04 -0.08	I ₁	d2	d ₃	d₄	I ₂	I ₃	I ₄	l₅ Unclamped		max.	min.	max.		
[mm]									[mm]	[N]	[°C]		[g]	
8	5 – 10	9.5	38	17.5	6.5	30.2	11	3	8	18	-30	80	26	22360.0022

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 23.01.2024.

Contains Proposition 65 substances



Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.