# Collar Nuts with Conical Seat 23080.0524



### **Product Description**

With this combination of fixture nut and conical seat, non-parallel clamping surfaces can be compensated.

The fixture nut with conical seat is a fixed unit consisting of fixture nut and conical seat with the following advantages / characteristics:

- Functionally reliable
- · Captive
- · Fast and efficient mounting
- Simplified storage
- Swivel range max. 3°

# Material

## Conical seat

· Heat-treated steel, tempered, blackened

#### Nut


· Heat-treated steel, tempered, blackened


#### More information

#### References

For torques and strengths please refer to appendix - Technical Data -

## Drawing






## picture 1

#### **Order information**

Dimensions			S	<b>I</b>	Art. No.
d <sub>1</sub>	d <sub>2</sub>	m		-	
		~			
	[mm]		[mm]	[g]	
with small bearing surface –	picture 1				
M24	44	42.5	36	259	23080.0524

## **Application example**



## Compliance

## **RoHS compliant**

Compliant according to Directive 2011/65/EU and Directive 2015/863.

#### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

## Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.