


Down-Hold Clamps • with cranked tension lever

23210.0325



No Photo
available

Product Description

The quick-acting clamping element simultaneously presses the workpieces towards both, the stops and fixture plate. The low profile construction enables the entire surface to be machined. In conjunction with cylindrical stops EH 23280., a special fixture can be replaced.

Material


- Steel, case-hardened, blackened

More information

Further products

- Stops, cylindrical


Drawing



Order information

T-slot size	d_1	a	b	d_2	Dimensions								Clamping force horizontal max.		Art. No.
[mm]					h_1	h_2	h_3	h_4	l_1	l_2	l_3	s	[kN]	[g]	
with flat clamping jaw, clamping to the left															
12	M12	11.6	48	12.5	38	63	16	62	190	72	40	4	7	868	23210.0325

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 23.01.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure
<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.