

Vertical Toggle Clamps · with horizontal base and solid support arm

23330.0204



Product Description

Due to their favourable power to movement ratio and their easy action the toggle clamps are versatile applicable for a wide range of uses.

These toggle clamps can be used in the metal working industry when drilling, welding, bending, grinding, testing and fitting as well as in the wood and plastic industry in glueing, drilling, cutting and milling jigs.

The "toggle" principle of the toggle clamp allows a large and quick opening of the clamp. If unclamped the workpieces are completely cleared for unimpeded removal. The large power transmission results maximum clamping force by low hand force. The clamps are self-arresting they remain locked, resisting the force produced when machining components.

The toggle clamps are manufactured from high quality components and are designed for maintenance-free continuous use.

An oil resistant ergonomic 2-component handle, with slip-proof, soft surface and large grip area for high ease of use.

Material

Clamp

- Steel, zinc-plated by galvanization, passivated

Rivet

- Stainless steel

Handle

- plastic

Clamping screw

- Steel, tempered, zinc-plated by galvanization


Clamping cap

- Rubber, black


Assembly

The clamping screw must be welded to the support arm in the desired position.


Drawing




23330.0204





23330.0205
23330.0207



23330.0206



Order information																								
Nominal size	Clamping screw	Dimensions																Holding force		α				Art. No.
		d_1	b_1	b_2	h_1	h_2	h_3	h_4	h_4	l_1	l_2	l_3	l_4	l_5	l_6	l_7	l_8	F_1	F_2		min.	max.		
	[mm]	[mm]																[kN]	[°C]		[g]			
Steel																								
4	M8 x 45	7.5	46	6	186	33.5	18	0	12	108.5	116.5	81	19.5	43	35	7.5	20	1.4	2.5	105°	-10	80	426	23330.0204

Compliance																							
RoHS compliant																							
Compliant according to Directive 2011/65/EU and Directive 2015/863.																							
Does not contain SVHC substances																							
No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.																							
Does not contain Proposition 65 substances																							
No Proposition 65 substances included.																							
https://www.P65Warnings.ca.gov/																							
Free from Conflict Minerals																							
This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.																							