

## Eccentric Quick Clamps • with female thread

23390.0001



### Product Description

For quick and easy clamping and releasing of workpieces.  
When using the "adjustable" design (picture 2) the lever position can be moved.

### Material

#### Support washer

- Thermoplastic PA, glass-fiber reinforced

#### Lever

- Zinc die-cast, plastic coated, black, similar to RAL 9005

#### Threaded part

- Steel, zinc-plated by galvanization


#### Inner parts

- Steel, zinc-plated by galvanization

#### Adjusting nut

- Steel, zinc-plated by galvanization


### Drawing



### Order information

Dimensions								Stroke s at 90° lever position	max.		Art. No.
l	d <sub>1</sub>	d <sub>3</sub>	d <sub>5</sub>	h <sub>2</sub> max.	b	t <sub>1</sub>	t <sub>2</sub> min. in clamping position	[mm]	[°C]	[g]	
[mm]											
with female thread – picture 1, Steel											
63	M6	16	18.5	16.4	16	13	3	0.75	80	58	23390.0001

## Application example



## Compliance

### RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

### Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 23.01.2024.

### Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure  
<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.