V-Block Elements right/left 1548.800





Product Description

Material

• Steel, case-hardened, ground

Drawing





ø-Area	Distance	X
40-330	1x50= 50	190
140-430	2×50=100	240
240-530	3x50=150	290
340-630	4×50=200	340
440-730	5x50=250	390
540-830	6×50=300	440
640-930	7×50=350	490
740-1030	8x50=400	540
840-1130	9×50=450	590

Order information

System		Dimer	1	Art. No.					
	b ₁	d ₁	s	а	_				
		[m	[g]						
left – picture 1									
L12	48	12	18	15	1308	1548.800			



www.halder.com Page 1 of 2 Published on: 3.2.2024

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2

Published on: 3.2.2024