# **T-Bolts ·** DIN 787 23030.0156



### **Product Description**

T-bolts when combined with DIN 6330 fixture nuts (EH 23070.) and DIN 6340 plain washers (EH 23060.) become complete clamping bolts. These T-bolts are characterised by the rolled thread.

#### **Material**

Heat-treated steel, black, forged, T-slot guidance milled

#### More information

#### Notes

Special types on request.


#### References

For torques and strengths please refer to appendix - Technical Data -

### **Further products**

- Shaft / Plain Washers, DIN 6340 heattreated
- Fixture Nuts, DIN 6330 (height 1,5 d)

Drawing



# Order information

T-slot size	ze Dimensions						Ĩ	Art. No. <sup>1)</sup>
	d	I	а	b	е	k		
[mm]		[mm]					[g]	
quality 8.8								
16	M14	250	15.6	150	25	9	301	23030.0156

<sup>1)</sup> DIN standards do not include these dimensions.

### **Application example**





# Compliance

# **RoHS compliant**

Compliant according to Directive 2011/65/EU and Directive 2015/863.

# Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.