T-Bolts • DIN 787 23030.0287



Product Description

T-bolts when combined with DIN 6330 fixture nuts (EH 23070.) and DIN 6340 plain washers (EH 23060.) become complete clamping bolts.

These T-bolts are characterised by the rolled thread.

Material

· Heat-treated steel, black, forged, T-slot guidance milled

More information

Notes

Special types on request.


References

For torques and strengths please refer to appendix - Technical Data -

Further products

- · Shaft / Plain Washers, DIN 6340 heat-
- Fixture Nuts, DIN 6330 (height 1,5 d)

Drawing



Erwin Halder KG

Order information

T-slot size	Dimensions						-	Art. No.
	d	l	а	b	е	k	_	
[mm]	[mm]						[g]	
quality 8.8								
28	M24	315	27.6	190	44	18	1275	23030.0287


Application example





www.halder.com Page 1 of 2

Published on: 3.2.2024



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Erwin Halder KG

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



n Page 2 of 2 Published on: 3.2.2024

www.halder.com