

## Clamps • DIN 6316 with goose-neck

### 23160.0027




#### Product Description

This clamp (clamping claw) according to DIN 6316 with goose-neck is mainly used in mechanical clamping technology for clamping workpieces.


#### Material

- Heat-treated steel, varnished


#### Drawing



#### Order information

Nominal dimension $b_1$ [mm]	$l$	$a$	$b_2$	Dimensions					For screws		 [g]	Art. No.
				$b_3$	$c$	$e_1$	$e_2$	$h$	[mm]	[in]		
26	250	35	70	35	28	72	80	70	M24	1	4115	23160.0027

#### Application example



## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.