Down-Hold Clamps • with cranked tension lever 23210.0341



Product Description

The quick-acting clamping element simultaneously presses the workpieces towards both, the stops and fixture plate. The low profile construction enables the entire surface to be machined. In conjunction with cylindrical stops EH 23280., a special fixture can be replaced.


Material


- Steel, case-hardened, blackened
- More information

Further products

· Stops, cylindrical








Order information

T-slot	Dimensions														I	Art. No.
size	d1	а	b	d₂	h1	h ₂	h ₃	h ₄	h₅	I1	l ₂	I ₃	s	force horizontal max.	-	
[mm]	[mm]														[g]	
with flat	vith flat clamping jaw, clamping to the right															
14	M12	13.6	48	12.5	38	40	16	62	19.1	190	72	40	4	7	858	23210.0341

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 23.01.2024.

Contains Proposition 65 substances

Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.