





The lower clamping jaw with pivot function (23320.0148 - picture 6) adapts to the profiles of the workpiece.





## Order information


Clamping range max. in combination with 23320.0050 [mm]	 [g]	Art. No.
15 – 27	88	23320.0056








upper exchange clamping jaw – picture 2

## Application example



e.g. Ball-Ended Thrust Screw (EH 22720.)





## Compliance

### RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.