

Retaining Latches · one-sided

24100.0102



Product Description

To be used for door locking, drawers and as handling aid etc.
The retaining catch is indexing 4 x 90°.

Material

Lever

- Zinc die-cast, black, similar to RAL 9005


Inner parts

- Dry powdered metal

Screw

- Stainless steel A2 (ISO 10642)


Drawing



Order information

| Dimensions | | | | | | | | | | WS | Load capacity max. |  | Art. No. |
|----------------|----------------|----------------|----------------|----|----------------|----------------|----------------|----------------|------|-----|-----------------------|---|----------|
| d ₁ | d ₂ | l ₁ | l ₂ | b | h ₁ | h ₂ | h ₃ | h ₄ | [mm] | | | | |
| black | | | | | | | | | | | | | |
| M6 | 9 | 45 | 55 | 19 | 12 | 13.3 | 0.8 | 6.5 | 4 | 500 | 60 | 24100.0102 | |

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.