Horizontal Toggle Clamps • with angle base

EH 23330.



Product Description

Due to their favourable power to movement ratio and their easy action the toggle clamps are versatile applicable for a wide rang of uses.

These toggle clamps can be used in the metal working industry when drilling, welding, bending, grinding, testing and fitting as well as in the wood and plastic industry in glueing, drilling, cutting and milling jigs.

The "toggle" principle of the toggle clamp allows a large and quick opening of the clamp. If unclamped the workpieces are completely cleared for unimpeded removal. The large power transmission results maximum clamping force by low hand force. The clamps are self-arresting they remain locked, resisting the force produced when machining components.

The toggle clamps are manufactured from high quality components and are designed for continuous use.

A oil resistant ergonomic 2-component handle, with increased grip area with soft surface for high ease of use.

The quickly adjustable clamping screws are provided by a retainer.

Material

Clamp

Steel, zinc-plated by galvanization, passivated

Rivet

· Stainless steel

Handle

· plastic

Clamping screw

Steel, tempered, zinc-plated by galvanization

Clamping cap


· Rubber, black


More information

References

Replacement clamping screws are available as accessories in the online shop.

Drawing







Erwin Halder KG

www.halder.com Page 1 of 2
Published on: 11.10.2023

Order information

Nominal	Clamping	Dimensions									Hole	ding	α	<u>[</u>	: 	I	Art. No.								
size	screw									force				ı											
		d ₁	b ₁	b ₂	b ₃	h₁	h ₂	h ₃	h ₄	h ₅	h ₅	h ₆	h ₇	h ₈	l ₁	l ₂	l ₃	I ₄	F ₁	F ₂		min.	max.		
										min.	max.														
	[mm]								[mr	m]									[k	N]		[°C	:]	[g]	
Steel																									
2	M5 x 30	5.2	31.0	5.0	19.0	68.0	49	57	10.0	14	20.0	13.5	8	28	120	32	4.0	18.5	0.8	1.1	90°	-10	80	154	23330.1022
3	M6 x 35	5.6	37.0	6.2	25.5	94.0	68	73	13.2	22	29.5	20.0	6	32	162	52	10.5	32.0	1.0	1.2	90°	-10	80	247	23330.1023
4	M8 x 45	6.8	42.5	8.0	28.5	86.5	86	70	15.0	5	16.0	24.0	7	38	206	59	6.5	37.0	1.8	2.5	90°	-10	80	400	23330.1024
5	M8 x 65	8.5	52.0	10.0	32.0	133.0	120	102	20.0	11	40.0	32.0	40	82	282	93	15.0	63.0	2.0	3.0	90°	-10	80	901	23330.1025

Accessories

	d ₂	I	Art. No.							
	[mm]	[g]								
Clamping screw (spare part of toggle clamp)										
	M5 x 30	11	23330.9002							
	M6 x 35	16	23330.9003							
	M8 x 45	38	23330.9005							
	M8 x 65	57	23330.9006							

Compliance

For detailed compliance information please select the desired article number.



Page 2 of 2 Published on: 11.10.2023