

Star Grip Screws • DIN 6336 plastic
EH 24740.



Product Description

Material


- Handle**
- DIN 7708 - thermosetting plastic (PF 31), black similar to RAL 9005
- Screw**
- Steel, zinc-plated by galvanization
 - Stainless steel A2

More information

Notes

Special types, e.g. differing lengths or screws from brass / stainless steel on request.

Drawing



Order information

Dimensions			 max. [°C]	 [g]	Art. No.
d ₁	d ₂ [mm]	l			
form L, Steel					
25	M 5	10	110	7.3	24740.0051
25	M 5	15	110	7.4	24740.0053
25	M 5	20	110	8.7	24740.0056
25	M 5	25	110	8.7	24740.0058
25	M 5	30	110	9.2	24740.0059
32	M 6	15	110	14.0	24740.0101
32	M 6	20	110	15.0	24740.0104
32	M 6	25	110	14.0	24740.0106
32	M 6	30	110	16.0	24740.0107
32	M 6	40	110	17.0	24740.0110
40	M 8	20	110	28.0	24740.0152
40	M 8	25	110	31.0	24740.0154
40	M 8	30	110	32.0	24740.0155
40	M 8	40	110	35.0	24740.0158
40	M 8	50	110	38.0	24740.0160
50	M10	25	110	51.0	24740.0202
50	M10	30	110	54.0	24740.0203
50	M10	40	110	60.0	24740.0206
50	M10	50	110	64.0	24740.0208
50	M10	60	110	73.0	24740.0209
63	M12	30	110	101.0	24740.0251
63	M12	40	110	108.0	24740.0254

Dimensions			 max. [°C]	 [g]	Art. No.
d ₁	d ₂ [mm]	l			
63	M12	50	110	115.0	24740.0256
63	M12	60	110	121.0	24740.0257
63	M12	80	110	143.0	24740.0260
80	M16	40	110	223.0	24740.0302
80	M16	50	110	237.0	24740.0304
80	M16	60	110	249.0	24740.0305
80	M16	80	110	274.0	24740.0308
form L, Stainless steel					
25	M 5	10	110	7.3	24740.1051
25	M 5	15	110	7.4	24740.1053
25	M 5	20	110	8.7	24740.1056
25	M 5	25	110	8.7	24740.1058
25	M 5	30	110	9.2	24740.1059
32	M 6	15	110	14.0	24740.1101
32	M 6	20	110	15.0	24740.1104
32	M 6	25	110	14.0	24740.1106
32	M 6	30	110	16.0	24740.1107
32	M 6	40	110	17.0	24740.1110
40	M 8	20	110	28.0	24740.1152
40	M 8	25	110	31.0	24740.1154
40	M 8	30	110	32.0	24740.1155
40	M 8	40	110	35.0	24740.1158
40	M 8	50	110	38.0	24740.1160
50	M10	25	110	51.0	24740.1202
50	M10	30	110	54.0	24740.1203
50	M10	40	110	60.0	24740.1206
50	M10	50	110	64.0	24740.1208
50	M10	60	110	73.0	24740.1209
63	M12	30	110	101.0	24740.1251
63	M12	40	110	108.0	24740.1254
63	M12	50	110	115.0	24740.1256
63	M12	60	110	121.0	24740.1257
63	M12	80	110	143.0	24740.1260
80	M16	40	110	223.0	24740.1302
80	M16	50	110	237.0	24740.1304
80	M16	60	110	249.0	24740.1305
80	M16	80	110	274.0	24740.1308

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.