Clamping Vices • moveable jaw

EH 1137.300



Product Description

Max. torque 140 Nm, clamping power F = 30 kN

Material


· Steel, case-hardened, ground

More information

Further products

- · Clamping Vices
- Clamping Vices, fixed jaw
- · Clamping Vices, replacement jaw, soft
- · Clamping Vices, replacement jaw, ribbed/flat

Drawing



Order information

System	ĭ	Art. No.
	[kg]	
V70	4	1137.300

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Erwin Halder KG

Does not contain Proposition 65 substances

No Proposition 65 substances included.

https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 1 of 1

Published on: 3.2.2024