Radio Transmitters • for retrieval unit EH 22810.



CE

Product Description

For cable-free transfer of the retrieval signal.

The radio transmitter is installed close to the retrieval unit, and connected to the bushing of the silicone cable. The transmitter makes the polled signal available by radio, and does not require additional cable connection. Power is supplied by a battery. The radio transmitter meets the requirements of protection class IP 67 (robust material) and is

therefore suitable for use with cooling lubricants. Frequency: 868.3 MHz (EU, Switzerland)

Other frequencies available on request.

More information


Notes

An AA battery (3.6 V) is included in the scope of delivery. Further information on request.

Further products

· Radio Receivers, for retrieval unit

Drawing



Order information

Dimensions						For art. no.	F	Art. No.			
I ₂	b ₂	h ₂	b ₁	d ₁	d ₂	h1	ե				
	[mm]							[g]			
universal	universal radio transmitter with protective caps										
98	64	52.5	36	M12 x 1	4.5	37	86	22810.0008 / .0012	288	22810.9010	

Accessories								
		Art. No.						
	[9]							
protection cap								
0	4.9	22810.9011						

Compliance

For detailed compliance information please select the desired article number.