# Extension Nuts • (height 3 d) EH 23090.



## **Product Description**

In comparison to a hexagon nut according to DIN 6330, the extension nuts are elongated and are particularly suitable as a connecting piece for stud bolts.

#### **Material**


• Heat-treated steel, tempered, quality 10, phosphated

### More information

#### References

For torques and strengths please refer to appendix - Technical Data -


## Drawing



#### **Order information**

Dimensions					Art. No.
d	e	m	s	-	
[mm]				[9]	
M 6	11.5	18	10	8.7	23090.0006
M 8	15.0	24	13	19.0	23090.0008
M10	18.5	30	16	35.0	23090.0010
M12	20.8	36	18	50.0	23090.0012
M14	24.2	42	21	79.0	23090.0014
M16	27.7	48	24	119.0	23090.0016
M20	34.6	60	30	228.0	23090.0020
M24	41.6	72	36	403.0	23090.0024
M30	53.1	90	46	819.0	23090.0030
M36	63.5	108	55	1386.0	23090.0036

# Application example



# Compliance

For detailed compliance information please select the desired article number.