Clamps • with flat-faced ball, similar to DIN 6314 EH 23180.



Product Description

This clamp (clamping claw) according to DIN 6314 with flat-faced ball is mainly used in mechanical clamping technology for clamping workpieces.

Material

Ball

· Ball-bearing steel, hardened, bright


· Heat-treated steel, blackened


More information

Notes

Ball protected against rotating.

Drawing





Order information


Nominal	Dimensions											I	Art. No.
dimension	I ₁	d ₃	a ₁	a ₂	b ₂	b ₃	e ₁	e ₂	h	l ₂	Ball diameter	_	
b ₁													
[mm]	[mm]											[g]	
6.6	50	5.8	10	2.5	20	8	10	20	1.6	5.0	8.5	60	23180.0007
9.0	60	7.2	12	3.0	25	10	13	22	2.0	6.5	10.0	109	23180.0009
11.0	80	8.6	15	3.5	30	12	15	30	2.7	7.5	12.0	218	23180.0011
13.0	125	10.5	20	4.0	40	14	21	50	3.5	10.5	16.0	616	23180.0014



Erwin Halder KG Page 1 of 2 www.halder.com

Published on: 6.4.2024

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Erwin Halder KG

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2

Published on: 6.4.2024