Locating Clamps EH 23230.



Product Description

Suitable for a simultaneous "positioning" and "clamping" of workpieces. The locating element is a precision element which can be assembled from either side. The clamping and locating part adapted to the workpiece is screwed to the cylindrical support. Clamping and locating parts are manufactured by the user according to the individual requirements.

Material


Handle


- Grey cast iron DIN 6335, orange plasticcoated
- Thermosetting plastic PF 31, black, DIN 319


Clamp

• Steel, case-hardened, blackened, ground

Drawing







lı

d₂


picture 1

Order information

	Dimensions															Ĩ	Art. No.
b ₁	b ₂	d₁	d ₂	d ₃	h ₁	h ₂	h ₃	I1	l ₂	l ₃	I ₄	I ₅	I ₆	I ₇	I ₈	_	
	±0.05	H7 g5															
	[mm]															[g]	
with pa	with palm grip – picture 1																
40	27	18	M6	40	29.8	14.9	16.9	50	19	9	8	-	33	17	28	505	23230.0040
50	33	22	M8	50	34.8	17.4	19.4	60	24	10	10	-	42	21	34	862	23230.0050
with sp	with spiral eccentric clamping lever – picture 2																
40	27	18	M6	-	29.8	14.9	16.9	60	19	3	8	50	96	17	28	566	23230.0440
50	33	22	M8	-	34.8	17.4	19.4	75	24	4	10	63	145	21	34	1071	23230.0450



Application example



For detailed compliance information please select the desired article number.