# **Standard Clamping Jaws** • for floating clamp M 12 EH 23320.



## **Product Description**

The clamping jaws can be used for floating clamps 23320.0008, 23320.0010, 23320.0012, and 23320.0014.


#### **Material**

• Case-hardened steel, nitrided, manganese phosphated

## Assembly

When using custom-made jaws, it is important to insert the tightening screw (M 8-12.9, 43 Nm) 10 mm deep into the clamp housing on the upper clamping jaw and 9 mm deep into the clamp housing on the lower clamping jaw.

# Drawing



\* Specifications and material of especially designed jaws have to be taken into consideration.

## **Order information**

Clamping range	Dimensions h <sub>1</sub> -0.1	Ĭ	Art. No.
[mm]	[mm]	[g]	
lower standard clamping jaw – picture 1			
-	26.8	99	23320.0050
upper standard clamping jaw – picture 2			
0 – 12	21.0	69	23320.0052

## Compliance

#### **RoHS compliant**

Compliant according to Directive 2011/65/EU and Directive 2015/863.

# **Does not contain SVHC substances** No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.