Vertical Toggle Clamps • with vertical base EH 23330.



Product Description

Due to their favourable power to movement ratio and their easy action the toggle clamps are versatile applicable for a wide rang of uses.

These toggle clamps can be used in the metal working industry when drilling, welding, bending, grinding, testing and fitting as well as in the wood and plastic industry in glueing, drilling, cutting and milling jigs.

The "toggle" principle of the toggle clamp allows a large and quick opening of the clamp. If unclamped the workpieces are completely cleared for unimpeded removal. The large power transmission results maximum clamping force by low hand force. The clamps are self-arresting they remain locked, resisting the force produced when machining components. The toggle clamps are manufactured from high quality components and are designed for

continuous use. A oil resistant ergonomic 2-component handle, with increased grip area with soft surface for high ease of use.

The quickly adjustable clamping screws are provided by a retainer.

Material

Clamp

 Steel, zinc-plated by galvanization, passivated

Rivet

Stainless steel

Handle

plastic

Clamping screw

• Steel, tempered, zinc-plated by galvanization

Clamping cap


· Rubber, black


More information


References

Replacement clamping screws are available as accessories in the online shop.

Drawing







23330.0014


0

۱,


l 8


dı


16



23330.0016







Order information

Nominal Clamping size screw				Dimensions													Holo for		α	[Ũ	Art. No.						
			d1	b ₁	b ₂	b ₃	h ₁	h ₂			h₄ max.	h ₅	h ₆	I1	l ₂	I ₃	I ₄	I ₅	I ₆	I ₇	I ₈	lg	F ₁	F ₂		min	max		
	[m	ım]		[mm]											[kN]			[°C]		[g]									
3	Μ6	x 35	5.5	21	6	5	144.5	38	12	11.5	19.5	28.5 – 32	30	78	80	52	11	25	6.0	20.0	32	12.5	0.8	1.2	60°	-10	80	197	23330.0013
4	M 8	x 45	7.5	27	8	6	200.0	48	18	16.5	25.0	41.0	-	112	114	79	19	36	7.5	20.0	40	_	1.2	2.5	60°	-10	80	417	23330.0014
5	M 8	x 65	8.6	35	10	8	244.0	65	20	16.5	45.5	55.5	-	141	130	101	16	54	13.0	32.0	53	-	1.7	3.0	60°	-10	80	689	23330.0015
6	M12	x 80	8.5	36	14	10	301.0	77	25	18.0	49.0	66.0	64	195	183	140	35	72	9.5	45.0	65	26.5 - 31.5	3.0	5.0	60°	-10	80	1511	23330.0016
7	M12	x 110	13.0	39	14	10	369.0	117	30	33.0	90.5	102.0	-	231	206	165	28	89	24.5	50.5	90	-	3.4	5.5	60°	-10	802	2000	23330.0017

Accessories

	d ₂	۲. ۲	Art. No.
	[mm]	[9]	
Clamping screw (spare p	art of toggle clamp)	!	
	M 6 x 35	16	23330.9003
	M 8 x 45	38	23330.9005
	M 8 x 65	57	23330.9006
	M12 x 80	147	23330.9007
	M12 x 110	170	23330.9008

Compliance

For detailed compliance information please select the desired article number.