Base Plates • suitable on pallets DIN 55 201

1100.700



Product Description

Material


- Steel, hardened, ground

More information

Notes

Special types on request.

Drawing




* These tolerances are valid only for optional exterior stop type.
Slot spacing 70 ±0,01.

Order information


System	Dimensions							For screws	y	Number of T-slots		Art. No.
	a_1 x a_2	c	d	l_1 ±0.013	l_2	l_3	l_4					
	[mm]							[mm]	[mm]		[kg]	
V70	400 x 400	50	20	150	60	100	100	M12	12	5 x 5	56	1100.700

Application example








HALDER




HALDER
HALDER





Compliance

RoHS compliant
Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances
No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Contains Proposition 65 substances
Nickel can cause cancer from exposure.
https://www.P65Warnings.ca.gov/

Free from Conflict Minerals
This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.