# **FERROPLEX Combi Hammer** • Locksmith's hammer and soft-face mallet in one EH 3677.



#### **Product Description**

Halder has engineered the FERROPLEX as a 2-in-1 combi hammer for all those who want to enjoy both the benefits of a steel hammer and the advantages of a soft-face mallet. The hammer head is made of premium heat-treated steel and carefully induction hardened on the impact surface.

The replaceable nylon insert on the opposite side offers outstanding impact qualities and is guaranteed to combine maximum strength with unique durability. It is composed of extruded and extremely homogeneous material. Compared to injection moulded plastic inserts, it is therefore considerably more wear-resistant and durable and will never chip even in sub-zero temperatures. The break-proof steel tube handle is encased with an ergonomic non-slip rubber grip. The FERROPLEX is available in sizes of D30mm with a total weight of 600g and D35mm with a total weight of 800g.

Product features:

- · 2-in-1 combi hammer (steel hammer plus soft-face mallet).
- Hammer head made of premium heat-treated steel, impact surface induction hardened.
- Replaceable insert made of special nylon with maximum strength.
- Break-proof steel tube handle with ergonomic non-slip rubber grip.
- Wear-resistant powder coating prevents corrosion.
- Available in sizes D30mm (600g) and D35mm (800g).

#### **Application Areas**

General mounting work in industry, crafts and the automotive sector, service and maintenance work, installation work

#### Material

#### Handle

• Steel tube and ergonomic rubber grip

#### Insert

- Nylon, white
- hard
- Very wear-resistant
- · no chipping (even at tempeatures below
- zero)
- noise-dampening
- very high impact

#### Hammer face


Heat-treated steel, induction hardened

#### **Order information**

Ø		Din —	nensions Length x Width x Height	Ĭ	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
[mm]				[g]				
30	104	290	290 x 104 x 30	600	4030618303039	AAA905c002	21-04-09-16	3677.030
35	104	295	295 x 104 x 35	800	4030618303046	AAA905c002	21-04-09-16	3677.035

### Application example





#### Compliance

#### **RoHS compliant**

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w Contains lead - SVHC list [REACH] as of 23.01.2024.

#### **Contains Proposition 65 substances**

## 

Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

#### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.

