# Ball Lock Pins • self-locking, with T-Handle 22350.0077



## **Product Description**

For quick fastening, locking, adjusting, changing and securing. Quickly and easily unlockable for frequently repeated connections.

All versions are corrosion resistant. When using stainless steel 1.4542: high-strength, hardened, abrasion resistant pin with high load capacity. Version with ergonomic grip.

#### Material

## Pin part

 Stainless steel 1.4542, precipitationhardened

#### Handle

Aluminium, black similar to RAL 9005

#### Press button

· Stainless steel, black

#### Spring

· Stainless steel

#### Operation

The balls are unlocked by pressing the button.

## Characteristic

Types from stainless steel 1.4542 with marking below the balls.

#### More information

## Notes

Special types on request.

• This product is also available in INCH dimensions.

#### Accessories

Can easily be fitted with retaining cable EH 22400.

# **Further products**

- Locating Bushings, for ball lock pins and socket pins
- Locating Bushings, with flange, for ball lock pins and socket pins
- Retaining Cables
- Positioning Bushings, with collar, DIN 172 A
- Positioning Bushings, without collar, DIN 179 A
- Ball Lock Pins with T-Handle, single acting comply with NAS / MS17985



\*\* Types from stainless steel 1.4542 with marking.

## **Order information**

<b>d</b> <sub>1</sub> -0.04 -0.08	Ι <sub>1</sub> +0.6	d <sub>2</sub>	d <sub>3</sub>	Dim I <sub>2</sub> ±1	ensions I <sub>3</sub>	I4	I <sub>5</sub>	I <sub>6</sub>	Location hole H11	min.	max.	Ă	Shearing resistance, two-shear <sup>1)</sup> min.	Art. No.	
[mm]									[mm]	[°C]		[g]	[kN]		
Stainle	Stainless steel														
16	45	19	23.4	14	42.2	29.8	74.8	24.7	16	-30	150	172	257	22350.0077	

<sup>1)</sup> Shearing resistance similar to DIN 50141

# **Application example**





# Compliance

## **RoHS compliant**

Compliant according to Directive 2011/65/EU and Directive 2015/863.

## Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

## Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.

