# **Centering Clamping Elements** • with clamping segments EH 23340.



## **Product Description**

For clamping and centering of workpieces with internal bore. Exact self centering with a precision of  $\pm 0,025$  mm. Due to the clamping segments being ground, workpieces with raw and/or machined surfaces can be frictionally connected, centered and held down at the seats. Large adjustment stroke and a low building height are a feature of the centering clamping element. **Mounting from either top or bottom.** 

#### **Material**

## **Body**

· Tool steel, hardened, blackened

#### Spring

Stainless steel

#### Clamping segments

Stainless steel 1.4112, hardened and ground

#### **Assembly**

Assembly instruction for mounting from above: Remove clamping plate and screw. Screw in threaded pin from below, and tighten from above using female WS<sub>2</sub>.


Further or detailed information can be found in the assembly and operating instructions.

#### More information

## **Further products**

- Centering Clamping Elements, with clamping balls
- Centering Clamping Elements, with clamping segments, operation from the bottom
- Centering Clamping Elements, with clamping balls, operation from the bottom

## **Drawing**



Erwin Halder KG

# **Order information**


Dimensions												Number of	Stroke	W	is (	Clamping	Tightening	ntening Location hole								Art. No.
<b>d</b> ₁ min.	<b>d</b> ₁ max.	d <sub>2</sub>	d <sub>3</sub>	<b>d</b> ₄ +0.3	h₁ -1	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	<b>h</b> ₅ -2	I₁ ±0.1	t	segments n	s	WS <sub>1</sub>	WS <sub>2</sub>	force F	torque max.	<b>D</b> ₁	D <sub>2</sub>	D <sub>3</sub>	D <sub>4</sub>		<b>H₂</b> +0.5	L <sub>1</sub>		
111111.	шах.	17		70.3	- 1				-2	±0.1						max.	1116711	П/					+0.5	±0.1		
	[mm]												[mm]	[m	m]	[kN]	[Nm]	[mm]						[g]		
14.5	18.5	12	M 4	2.0	14.3	9.8	8.6	5.5	19.3	4.5	6	3	2.3	3	5	3.5	5	12	2.0	4	M 4	2.0	5.5	4.5	26	23340.0014
18.5	22.5	15	M 5	2.5	16.6	11.5	10.4	7.5	22.8	5.5	7	3	2.3	4	5	4.5	10	15	2.5	5	M 5	2.5	7.5	5.5	45	23340.0018
22.5	26.5	20	M 6	3.0	19.7	14.1	13.0	6.0	28.7	7.0	8	3	2.3	5	6	5.0	17	20	3.0	6	M 6	3.0	6.0	7.0	72	23340.0022
26.5	30.5	20	M 6	3.0	19.9	14.2	13.0	6.0	28.9	7.0	8	3	2.3	5	6	5.0	17	20	3.0	6	M 6	3.0	6.0	7.0	96	23340.0026

www.halder.com Page 1 of 2

Published on: 10.8.2024

Dimensions											Number of	Stroke	Stroke WS			ClampingTightening			Lo	catio	I	Art. No.				
<b>d</b> <sub>1</sub> min.	<b>d</b> ₁ max.	<b>d</b> <sub>2</sub> f7		<b>d</b> ₄ +0.3	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	h <sub>5</sub>	<b>I</b> ₁ ±0.1	t	segments n	s	WS <sub>1</sub>	WS <sub>2</sub>	force F max.	torque max.	<b>D</b> ₁ H7	D <sub>2</sub>	D <sub>3</sub>	D <sub>4</sub>	H₁	<b>H</b> <sub>2</sub> +0.5	<b>L</b> ₁ ±0.1		
[mm]										[mm] [mm]			[kN]	[Nm]	[mm]				m]			[g]				
30.5	38.5	25	M 6	4.0	23.2	14.0	11.7	7.0	32.2	9.0	8	3	4.6	5	6	5.0	17	25	4.0	6	M 6	4.0	7.0	9.0	131	23340.0030
38.5	46.5	30	M 8	4.0	27.2	18.0	15.5	7.5	39.2	11.0	10	6	4.6	6	8	6.5	43	30	4.0	8	M 8	4.0	7.5	11.0	259	23340.0038
46.5	54.5	30	M 8	4.0	27.2	18.0	15.7	7.5	39.2	11.0	10	6	4.6	6	8	6.5	43	30	4.0	8	M 8	4.0	7.5	11.0	348	23340.0046
54.5	70.5	45	M10	5.0	40.7	23.7	19.1	9.0	54.7	15.0	12	6	9.2	8	10	8.0	79	45	5.0	10	M10	5.0	9.0	15.0	675	23340.0054
70.5	86.5	60	M12	5.0	46.0	28.3	23.6	10.0	63.0	17.0	15	6	9.2	10	12	10.0	141	60	5.0	12	M12	5.0	10.0	17.0	1346	23340.0070
86.5	102.5	60	M16	5.0	51.1	30.3	25.6	10.0	72.1	25.0	15	6	9.2	14	17	10.0	354	60	5.0	16	M16	5.0	10.0	25.0	2000	23340.0086

# **Application example**



# Compliance

# RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

# Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 27.06.2024.

## **Does not contain Proposition 65 substances**

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

## **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Page 2 of 2 Published on: 10.8.2024