Spring Plungers • headed, with ball and internal hexagon 22030.0931



Product Description

Spring plungers can be used for locating or for applying pressure, as a detent or for ejection. Precise screwing depth due to head.

Material

Body

· Free cutting steel, blackened

· Ball-bearing steel, hardened

Spring

Stainless steel

Assembly

Respect dimension I₃ for M 4 / M 5.

Standard spring load: no marking





Standard spring load

Heavy spring load

More information


Notes


Special types on request. Spring plungers are specially tested for spring range and forces.

References

Thread lock on request, please refer to appendix - Technical Data -Calculation of indexing resistance, please refer to appendix - Technical Data -

Drawing





Size M4+M5

Size M6-M12

Order information

Dimensions						ws	Stroke	Sprir	ng load ¹⁾		I	Art. No.
d ₁	d ₂	d ₃	I ₁	l ₂	I ₃		S	F ₁ ~	F ₂ ~	max.		
[mm]						[mm]	[mm]		[N]	[°C]	[9]	
free cutting steel, standard spring load												
M5	3	8	14	10	8.2	2.5	0.9	8	14	250	2.3	22030.0931


¹⁾ statistical average value

Erwin Halder KG

www.halder.com Page 1 of 2

Published on: 3.2.2024

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 23.01.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

www.halder.com Page 2 of 2 Published on: 3.2.2024