# Ball Lock Pins • self-locking, with L-handle 22350.0166



#### **Product Description**

For quick fastening, locking, adjusting, changing and securing. Quickly and easily unlockable for frequently repeated connections.

All versions are corrosion resistant. When using stainless steel 1.4542: high-strength, hardened, abrasion resistant pin with high load capacity. Version with ergonomic grip.

#### Material

#### Pin part

 Stainless steel 1.4542, precipitationhardened

#### Handle

Aluminium, black similar to RAL 9005

#### Press button

· Stainless steel, black

#### Spring

· Stainless steel

#### Operation

The balls are unlocked by pressing the button.

## Characteristic

Types from stainless steel 1.4542 with marking below the balls.

#### More information

## Notes

Special types on request.


• This product is also available in INCH dimensions.

#### Accessories

Can easily be fitted with retaining cable EH 22400.

## **Further products**

- Locating Bushings, for ball lock pins and socket pins
- Locating Bushings, with flange, for ball lock pins and socket pins
- Retaining Cables
- Positioning Bushings, with collar, DIN 172 A
- Positioning Bushings, without collar, DIN 179 A
- Ball Lock Pins with L-handle, single acting comply with NAS / MS17986



\*\* Types from stainless steel 1.4542 with marking.

Drawing

## Order information

d <sub>1</sub>	Dimensions d <sub>1</sub>   l <sub>1</sub>   d <sub>2</sub>   d <sub>3</sub>   l <sub>2</sub>   l <sub>3</sub>   l <sub>4</sub>   l <sub>5</sub>   l <sub>6</sub>   l <sub>7</sub>										min. max.		Ĩ	Shearing resistance,	Art. No.
-0.04 -0.08	+0.6	-2	-3	±1	-3	-4	-5	-0						<b>two-shear<sup>1)</sup></b> min.	
[mm]										[mm]	[°C]		[g]	[kN]	
Stainle	ess ste	el													
12	30	14.5	18.2	10.6	35.1	22.7	57.1	20.2	12.6	12	-30	150	78	144	22350.0166

<sup>1)</sup> Shearing resistance similar to DIN 50141

## Application example





## Compliance

## **RoHS compliant**

Compliant according to Directive 2011/65/EU and Directive 2015/863.

## Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

## Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

### Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.