# **Centering Clamping Mandrels**

23340.0108



## **Product Description**

The centering clamping mandrels are often used in mechanical engineering. However, thanks to their simple operation and quick assembly, they can be used in all industries.

Centering clamping mandrels are used for centering and clamping of workpieces with a locating

The centering clamping mandrels have the following characteristics:

- Very high accuracy for turning/milling processes
- Ideal for secondary operations on turned parts
- Hardened and coated screw for long service life
- · Clamping body can be machined very easily (for adaptation to bore diameter)

#### **Material**

### **Body**

· Steel, blackened

### Clamping screw

· Case-hardened steel, case-hardened

#### **Assembly**

The centering clamping mandrel can be machined to the required seating diameter (e.g. by turning/milling). It must be noticed that before machining the centering clamping mandrel, it will be expanded approx. 0.1 mm over the clamping diameter. To machine the mandrel, a nut will be provided.

Further or detailed information can be found in the assembly and operating instructions.

#### More information


#### **Notes**

Special types on request.

#### **Further products**

· Centering Clamping Mandrels, with lateral handling

## **Drawing**



Erwin Halder KG


#### **Order information**

	Dime	ension	6				Number of	ws		Clamping	Tightening	Location	I	Art. No.				
d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	d <sub>6</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	I <sub>1</sub>	l <sub>2</sub>	segments	WS₁	WS <sub>2</sub>		torque	hole		
	min.	-0.05							~					max.	max.	H7		
[mm]												[m	m]	[kN]	[Nm]	[mm]	[g]	
20	13.5	37.5	МЗ	29	M8	24.9	19	15	6	14	6	6	2	8	24	37.5	99	23340.0108



Page 1 of 2 Published on: 22.2.2024

## **Application example**



## Compliance

## **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

## Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

## **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 22.2.2024

Erwin Halder KG