# Ball-Ended Thrust Screws • headed, flat-faced ball



# **Product Description**

Ball-ended thrust screws can also be used for clamping, tightening or supporting of non-parallel surfaces.

The flat-faced, movable ball enables a flat load transmission.

#### Material

## Ball

· Ball-bearing steel, hardened

#### Screw

Heat-treated steel, 1200 ±100 N/mm<sup>2</sup>

#### More information

#### Notes

Ball not secured against rotating. Special types on request.


#### References

Thread lock on request, please refer to appendix - Technical Data -

## **Further products**

• Ball-Ended Thrust Screws, headed, ball protected against rotating

# **Drawing**



# Order information

Dimensions							ws	Load capacity	I	Art. No.
d <sub>1</sub>	l <sub>2</sub>	d <sub>2</sub>	d <sub>3</sub>	l <sub>3</sub>	I <sub>4</sub>	Ball diameter		for static load <sup>1)</sup>		
	~							max.		
[mm]							[mm]	[kN]	[9]	
									101	
bearing surfa	ce ribbed,	Heat-treate							101	

<sup>1)</sup> Statements on load capacity are not valid for the stainless steel type.

# Compliance

### **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

# Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Erwin Halder KG

# Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

# **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 1 of 1
Published on: 3.2.2024