# **Down-Thrust Clamps** • swivelling, size 82.5

23310.0070



# **Product Description**

The down-thrust clamp is a universal mechanical clamp that allows fast and easy exchange and clamping of workpieces - as the clamping claw can be easily manually swivelled to clear the workpiece.

The down-thrust clamps have the following advantages:

- Compact design
- Clamping force of up to max. 30 kN via a clamping screw WS 36
- Clamping claw swivels 360°
- Clamping stroke 30 mm
- Clamping height max. 250 mm Integrated clamping height stop for safe use
- Easy and quick workpiece change by swivelling the clamping claw to the left or right. The positioning ring 23310.0351 allows infinitely variable adjustment and permits precise repeat

#### **Material**

· Case-hardened steel, case-hardened, blackened and ground

#### **Assembly**

Fixture via 4 cap screws M 24 with a hole spacing 100 x 100 mm

#### More information


#### References


The clamping height can be reduced by using clamping inserts, e.g. EH 22730.

#### **Further products**

- · Positioning Rings, for down-thrust clamp
- Wrenches

## **Drawing**






Erwin Halder KG Page 1 of 2 www.halder.com

Published on: 3.2.2024

### **Order information**

|                | Dimensions     |                |                |                |                |                |                |       |                |                |                |                |                |                |                | Strok€ | Clamping | Tightening | I    | Art. No.   |
|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|-------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|--------|----------|------------|------|------------|
| d <sub>1</sub> | b <sub>3</sub> | b <sub>4</sub> | d <sub>2</sub> | d <sub>3</sub> | d <sub>4</sub> | h <sub>1</sub> | h <sub>2</sub> | $h_3$ | h <sub>4</sub> | h <sub>5</sub> | I <sub>1</sub> | l <sub>2</sub> | l <sub>3</sub> | I <sub>4</sub> | I <sub>5</sub> |        | force    | torque     |      |            |
|                |                |                |                |                |                |                |                |       |                |                |                |                |                |                |                |        |          | max.       |      |            |
|                | [mm]           |                |                |                |                |                |                |       |                |                |                |                |                |                |                | [mm]   | [kN]     | [Nm]       | [kg] |            |
| 82.5           | 155            | 100            | M24            | M20            | 49             | 220 – 250      | 300 – 330      | 30    | 90             | 65             | 49             | 115            | 91.5           | 148            | 100            | 30     | 30       | 200        | 21   | 23310.0070 |

# **Application example**



## Compliance

### **RoHS** compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

# Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 23.01.2024.

# **Contains Proposition 65 substances**



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

## **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 3.2.2024