

Rubber Metal Buffers

25150.0206



Product Description

To be used for elastic bearing of motors, compressors, pumps etc.
The hardness is $55 \pm 5^\circ$ shore A. Further shore hardnesses ($40 \pm 5^\circ$ shore A and $70 \pm 5^\circ$ shore A) on request.

Material

Support washer

- Steel, zinc-plated, blue chromated

Threaded bushing

- Steel, zinc-plated, blue chromated


Body

- Rubber natural caoutchouc (NR), black


Screw

- Steel, zinc-plated, blue chromated


Drawing



picture 1





picture 2




picture 3

Order information

Dimensions					Spring rate R	Load capacity	Spring range			Art. No.	
d ₁	l ₁	d ₂	l ₂	s	~	max.	min.	max.			
±1.5	±1.5										
[mm]					[N/mm]	[N]	[mm]	[°C]	[g]		
with screw, on both sides – picture 3											
10	10	M4	10	1.2	36	89	2.5	-30	80	3	25150.0206

Application example



Compliance

RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 23.01.2024.

Contains Proposition 65 substances



Lead can cause cancer and reproductive harm from exposure
<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.