# Ball Lock Pins • single acting - comply with NAS / MS17987

# 4213.B04



# **Product Description**

Ball Lock Pins according to MS17987 / NAS1333-1343 are used for quick fastening, locking, adjusting, changing and securing. Quickly and easily unlockable for frequently repeated connections.

Ball Lock Pins (Quick Release Pins) are produced according to Aviation Norm MS / NAS and tested to NAS 1332.

Protective treatment:

- All CRES parts are passivated according AMS2700 Heat treatment:
- Body: Rc. 40 min. (AMS2759, Condition H900)
- Spindle: Rc. 40 min. (AMS2759, Condition H900)
- Ball: Rc. 58-62 min. (AMS2759)

#### **Material**

#### **Body**

 Stainless steel, precipitation-hardened, passivated - CRES 17-4PH (specification AMS5643)

# Spindle

 Stainless steel, precipitation-hardened, passivated - CRES 17-4PH (specification AMS5643)

#### Spring

 Stainless steel, passivated - CRES 302 (specification ASTM-A-313)

#### Handle

 Stainless steel, passivated - CRES 17-4PH (specification AMS5643)

# Attaching ring

 Stainless steel, passivated - CRES 302 (specification ASTM A-313/A313M)

## Press button

 Stainless steel, passivated - CRES 303 (specification ASTM A484/484M)

### Ball

 Stainless steel, precipitation-hardened, passivated - CRES 440C (specification AMS5630)

# Operation

Ball lock pins single acting are self-locking and require a push of the button to release the balls.

### More information


# **Notes**

All further dimensions are available on request.

Other diameter / length combinations not listed which comply with the standard can be produced at short notice on customer request. Special types on request.

This product is manufactured in INCH dimensions.

# **Drawing**



Erwin Halder KG www.halder.com Page 1 of 2

Published on: 3.2.2024

# **Order information**

Nominal diameter A	A min.	A max.	Clamping length L +0.02		С	D max.	E max.	<b>F</b> min.	<b>G</b> max.	H min.	<b>J</b> min.	Location hole max.	Shearing resistance, two-shear min.	min.	max.		Standard description	Art. No.
	[in]													[°	F]	[g]		
1/4	0.247	0.2485	0.4	0.289	0.29	0.31	0.53	1.06	1.5	0.78	0.08	0.254	9,200	-65	200	224	MS17987C404 / IAS1334C6C04[	4213.B04

# Compliance

# **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

# Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

# Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

# **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

www.halder.com Page 2 of 2

Published on: 3.2.2024