# **Down-Thrust Clamps** • swivelling, size 40

23310.0054



### **Product Description**

Universal mechanical clamping element for fast and comfortable changing and clamping of workpieces by means of manually swivelling clamping claw.

The clamps have the following advantages:

- Rapid manual clamping by means of clamping screw, adjustable clamping lever, or double
  eccentric lever.
- Easy and rapid changing of workpieces by swinging away the clamping claw to the left or right.
   The positioning ring 23310.0350 allows infinitely variable adjustment.
- Continuously variable setting by means of positioning ring 23310.0350.
- The use of positioning ring 23310.0350 allows a repeatable precise clamping. Here h<sub>1</sub> min. increases by at least 7 mm (stroke minus 7 mm).
- · Compact design, thus only a small amount of space is required for clamping.
- Easy adjustment even to large clamping heights due to the height adjusting cylinders. As the force applied by the operator is not known for the versions with levers, the clamping force is given in the tables as a guide value. The average value was determined by tests.

#### Material

### Clamp

 Case-hardened steel, case-hardened, blackened and ground

#### Assembly

Down-thrust clamps can be attached in two ways:

- 1. in a T-slot, using a nut for T-slots DIN 508 (EH 23010.)
- 2. with the set screw directly in the mounting plate of, for example, a fixture

The cylinder must make contact over the whole surface.

Exceeding of the clamping height is inhibited by the height limitation.

#### More information

#### References

The clamping height can be increased by using height adjusting cylinders EH 23310. and disks EH 1107. and EH 1108. It can be reduced by employing clamping inserts, e.g. EH 22730.

### **Further products**


- · Positioning Rings, for down-thrust clamp
- · Height Adjusting Cylinders
- Spacers
- Wrenches





Erwin Halder KG www.halder.com Page 1 of 4


Page 1 of 4 Published on: 6.4.2024

# **Drawing**










# **Order information**

Dimensions												Stroke	Clamping	Tightening	I	Art. No.
d <sub>1</sub>	b <sub>1</sub>	b <sub>2</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	I <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>		force	torque max.		
[mm]												[mm]	[kN]	[Nm]	ra-1	
					[	J						[]	[KIA]	[INIII]	[g]	
with cla	amping	screw -	picture 2		[	<u>,                                      </u>						[]	[KN]	[MIII]	[9]	

# Application example





# Compliance

# **RoHS** compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

### Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 23.01.2024.

### **Contains Proposition 65 substances**



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG www.halder.com Page 4 of 4
Published on: 6.4.2024