Spring Plungers • headed, with ball and internal hexagon 22030.0941



Product Description

Spring plungers can be used for locating or for applying pressure, as a detent or for ejection. Precise screwing depth due to head.

Material

Body

Stainless steel 1.4305

Ball

· Stainless steel, hardened

Spring

Stainless steel

Assembly

Respect dimension I_3 for M 4 / M 5.

Characteristic

Standard spring load: no marking





Heavy spring load

Standard spring load

More information


Notes


Special types on request. Spring plungers are specially tested for spring range and forces.

References

Thread lock on request, please refer to appendix - Technical Data -Calculation of indexing resistance, please refer to appendix - Technical Data -

Drawing





Size M6-M12


Size M4+M5

Order information

Dimensions						ws	Stroke	Sprir	ng load ¹⁾	ß	Ĩ	Art. No.
d ₁	d ₂	d ₃	I ₁	l ₂	I₃ min.		S	F₁ ~	F ₂	max.		
[mm]						[mm]	[mm]		[N]	[°C]	[g]	
stainless steel, standard spring load												
M5	3	8	14	10	8.2	2.5	0.9	8	14	250	2.3	22030.0941

¹⁾ statistical average value

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.