

## Index Plungers • without hexagon collar

22120.0446



## Product Description

Index plungers are used for indexing bores.

## Material

## Body

- Stainless steel 1.4305

## Locking pin

- Stainless steel 1.4305, nickel-plated

## Knob

- Thermoplastic PA 6, black

## Assembly

Suitable mounting tools are available.

## More information

## Notes


Knob not removable.

Lock nuts have to be purchased separately.



## Further products

- Mounting Blocks, for index bolts and index plungers, die-cast
- Locating Bushings, for index bolts and index plungers
- Distance Collars, for index plungers

## Drawing






## Order information


Dimensions						Spring load <sup>1)</sup>				Art. No.	
d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	F <sub>1</sub>	F <sub>2</sub>	min.	max.		
-0.02			~	min.		~	~				
-0.05											
[mm]						[N]		[°C]		[g]	
with knob – picture 1, Stainless steel											
6	M12 x 1,5	25	54.5	6	26	6.5	19	-30	80	27	22120.0446

<sup>1)</sup> statistical average value

## Accessories

	Dimensions $d_2$ [mm]	Wrench size [mm]	 [g]	Art. No.
Lock nuts ISO 8675 (DIN 439), Stainless steel				
	M12 x 1,5	18	7.5	22120.0516
assembly tool, Steel				
	M12 x 1,5	–	14.0	22120.0956

## Application example



## Compliance

## RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

## Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

## Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

## Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.