# Ball Lock Pins • self-locking, with T-Handle

22350.0054



# **Product Description**

For quick fastening, locking, adjusting, changing and securing. Quickly and easily unlockable for frequently repeated connections.

All versions are corrosion resistant. When using stainless steel 1.4542: high-strength, hardened, abrasion resistant pin with high load capacity. Version with ergonomic grip.

### Material

### Pin part

 Stainless steel 1.4542, precipitationhardened

#### Handle

• Aluminium, black similar to RAL 9005

### Press button

· Stainless steel, black

### **Spring**

· Stainless steel

### **Operation**

The balls are unlocked by pressing the button.

### Characteristic

Types from stainless steel 1.4542 with marking below the balls.

### More information

### **Notes**

Special types on request.

This product is also available in INCH dimensions.


#### **Accessories**

Can easily be fitted with retaining cable EH 22400.

### **Further products**

- Locating Bushings, for ball lock pins and socket pins
- Locating Bushings, with flange, for ball lock pins and socket pins
- Retaining Cables
- Positioning Bushings, with collar, DIN 172 A
- Positioning Bushings, without collar, DIN 179 A
- Ball Lock Pins with T-Handle, single acting comply with NAS / MS17985

## **Drawing**



\*\* Types from stainless steel 1.4542 with marking.

Erwin Halder KG

www.halder.com


Published on: 6.4.2024


### **Order information**

Dimensions											I	Shearing resistance,	Art. No.		
<b>d</b> <sub>1</sub> -0.04 -0.08	l <sub>1</sub> +0.6	d <sub>2</sub>	d <sub>3</sub>	l <sub>2</sub> ±1	l <sub>3</sub>	I <sub>4</sub>	l <sub>5</sub>	I <sub>6</sub>	hole H11	min.	max.		two-shear <sup>1)</sup> min.		
[mm]									[mm]	[°C]		[g]	[kN]		
Stainle	Stainless steel Stainless steel														
10	80	12	14.7	9.6	35.8	26.9	51.5	15.8	10	-30	150	79	100	22350.0054	

<sup>1)</sup> Shearing resistance similar to DIN 50141

# **Application example**





# Compliance

# **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

# Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG www.halder.com Page 2 of 2