

Mounting Pads • protected against slipping
22590.1595



Product Description

Mounting pads can be used as foot or thrust pad. Not parallel bearing surfaces up to 15° degrees can be compensated.
The plastic cover on the mounting pad prevents slipping.

Material

Ball element with bolt
• Stainless steel 1.4305

Rubber cap
• Rubber, black

Lock nut
• Stainless Steel A2, ISO 4032


Pad
• Thermoplastic POM, white

More information


Notes

For the versions $d_1 = M10$ and $M12$ the lock nut conforms to DIN 934.

Drawing



Order information

d ₁	l ₁	Dimensions				WS	Load capacity for static load max.		Art. No.
		d ₂	l ₂	h ₁	h ₂				
		[mm]							
pad from thermoplastic, ball element with bolt from stainless steel – picture 2, Thermoplastic									
M24	100	69	91	55	24	36	25	718	22590.1595

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.