

Poignées fixes · DIN 39
EH 24450.




Description produit


Matières

- acier, tourné, zingué par galvanisation, passivé
- inox 1.4404


Plan



croquis 1



croquis 2




croquis 3

Informations détaillées

| d ₁ | d ₂ h8 | d ₃ | Dimensions | | | SW | [g] | Référence article | |
|---|----------------------|----------------|-------------------------------|---------------------|----------------|----|-----|-------------------|----------------------------|
| | | | d ₄ h13 [mm] | l ₁ ~ | l ₂ | | | | l ₃ |
| avec tenon lisse, forme D – croquis 1, acier | | | | | | | | | |
| 16 | 7 | – | 10 | 50 | 11 | 7 | – | 45 | 24450.0016 |
| 20 | 8 | – | 13 | 64 | 13 | 8 | – | 92 | 24450.0020 |
| 25 | 10 | – | 16 | 80 | 14 | 10 | – | 179 | 24450.0025 |
| 32 | 13 | – | 20 | 100 | 21 | 13 | – | 356 | 24450.0032 |
| 36 | 16 | – | 22 | 112 | 26 | 14 | – | 519 | 24450.0036 |
| filetée, forme E – croquis 2, acier | | | | | | | | | |
| 16 | – | M 6 | 10 | 50 | 11 | 7 | 3 | 43 | 24450.0116 |
| 20 | – | M 8 | 13 | 64 | 13 | 8 | 4 | 88 | 24450.0120 |
| 25 | – | M10 | 16 | 80 | 14 | 10 | 5 | 175 | 24450.0125 |
| 32 | – | M12 | 20 | 100 | 21 | 13 | 6 | 340 | 24450.0132 |
| 36 | – | M16 | 22 | 112 | 26 | 14 | 8 | 509 | 24450.0136 |
| filetée, forme E – croquis 3, inox | | | | | | | | | |
| 16 | – | M 6 | 10 | 50 | 11 | 7 | – | 45 | 24450.0316 |
| 20 | – | M 8 | 13 | 64 | 13 | 8 | – | 92 | 24450.0320 |
| 25 | – | M10 | 16 | 80 | 14 | 10 | – | 186 | 24450.0325 |

Exemple d'application



Conformité

Pour obtenir les informations détaillées sur la conformité choisissez le numéro d'article souhaité.