

SUPERCRAFT sledge hammers • with vibration-reducing, ergonomic and varnished Hickory handle
EH 3366.



Product Description

The tubular head of the SUPERCRAFT sledge hammers is filled with steel shot. The resulting effect is that the energy of the steel shot is transferred with a slight delay when the mallet's contact surface hits the workpiece. The reduced rebound allows the impact energy to be absorbed with perfect efficiency. The result is impact of exceptional magnitude. What is more, SUPERCRAFT sledge hammers allow for work with greatly improved safety, reduced strain on the joints and greater noise-dampening when compared to ordinary steel mallets. The inserts offer outstanding impact qualities and are guaranteed to combine maximum strength with unique durability. They consist of extruded and extremely homogeneous material. Compared to injection moulded plastic inserts, they are therefore considerably more wear-resistant and durable and will never chip even in sub-zero temperatures. The ergonomically shaped, varnished and ultra stable hickory handle is exceptionally rugged and has a vibration-dampening effect. The handle protection sleeve acts as an overstrike protector. A secure handle-head connection is ensured by an aluminium wedge and a safety pin. The wear-resistant powder coating prevents corrosion. Handle and inserts are replaceable. This version is available in three sizes: D80mm with a total weight of 4,410g, D100mm with a total weight of 7,050g, and D100mm with a total weight of 9,300g. Product features:

- Non-rebound, for extra powerful strikes.
- Noise-dampening and gentle on the joints.
- Inserts made of special nylon with maximum strength.
- Vibration-dampening, ergonomically shaped, very stable and varnished hickory handle.
- Handle protection sleeve acts as an overstrike protector.
- Handle and inserts replaceable.
- Available in D80mm (total weight 4,410g), D100mm (total weight 7,050g), and D100mm (total weight 9,300g).

Application Areas

Formwork, hall construction, steel construction, exhibition stand construction, concrete formwork, scaffold construction, tent construction, fence construction, driving steel wedges, straightening work, maintenance working, changing stucked tires

Material





Handle

- Hickory

Inserts

- Nylon, white
- hard
- Very wear-resistant
- no chipping (even at temperatures below zero)
- noise-dampening
- very high impact

Order information

Ø	Dimensions			Length x Width x Height	 [g]	GTIN	profil@ss 5.0	ecl@ss 10.1	Art. No.
									
80	200	880		880 x 200 x 80	4410	4030618301851	AAA938c002	21-04-09-20	3366.081
100	210	1000		1000 x 210 x 100	7050	4030618301868	AAA938c002	21-04-09-20	3366.107
100	265	1000		1000 x 265 x 100	9300	4030618303879	AAA938c002	21-04-09-20	3366.110

Application example









Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.