

Boutons cylindriques EH 24520.




Description produit

Matières

- acier bruni
- inox 1.4305, mat

Plan




Informations détaillées

Dimensions							Référence article
d ₁	d ₂	d ₃	h ₁	h ₂	t min.		
[mm]							
non moleté – croquis 1, acier							
21	M 4	12,5	18,0	10,5	10	26	24520.0002
21	M 5	12,5	18,0	10,5	10	25	24520.0003
25	M 6	14,5	22,5	14,0	12	42	24520.0005
25	M 8	14,5	22,5	14,0	12	38	24520.0006
31	M 8	18,5	27,0	17,0	15	75	24520.0008
31	M10	18,5	27,0	17,0	17	70	24520.0009
moleté – croquis 2, acier							
21	M 4	12,5	18,0	10,5	10	26	24520.0022
21	M 5	12,5	18,0	10,5	10	25	24520.0023
25	M 6	14,5	22,5	14,0	12	42	24520.0025
25	M 8	14,5	22,5	14,0	12	39	24520.0026
31	M 8	18,5	27,0	17,0	15	75	24520.0028
31	M10	18,5	27,0	17,0	17	70	24520.0029
non moleté – croquis 1, inox							
21	M 4	12,5	18,0	10,5	10	26	24520.0102
21	M 5	12,5	18,0	10,5	10	25	24520.0103
25	M 6	14,5	22,5	14,0	12	42	24520.0105
25	M 8	14,5	22,5	14,0	12	38	24520.0106
31	M 8	18,5	27,0	17,0	15	75	24520.0108
31	M10	18,5	27,0	17,0	17	70	24520.0109

Dimensions							Référence article
d ₁	d ₂	d ₃	h ₁	h ₂	t min.		
[mm]							
moleté – croquis 2, inox							
21	M 4	12,5	18,0	10,5	10	26	24520.0122
21	M 5	12,5	18,0	10,5	10	25	24520.0123
25	M 6	14,5	22,5	14,0	12	42	24520.0125
25	M 8	14,5	22,5	14,0	12	39	24520.0126
31	M 8	18,5	27,0	17,0	15	75	24520.0128
31	M10	18,5	27,0	17,0	17	70	24520.0129

Exemple d'application



Conformité

Pour obtenir les informations détaillées sur la conformité choisissez le numéro d'article souhaité.