# **Ball-Ended Thrust Screws •** headless, short

# 22720.0692



## **Product Description**

Ball-ended thrust screws, short execution, are particularly suitable for parallel shanks DIN 1835 E in combination, for instance, with Whistle Notch and Weldon Tool Holding Fixtures. Ball-ended thrust screws can also be used for clamping, tightening or supporting of non-parallel

The flat-faced, movable ball enables a flat load transmission.

#### Meterial

### Ball

· Ball-bearing steel, hardened

#### Screw

Heat-treated steel, 1200 ±100 N/mm<sup>2</sup>

### More information

#### **Notes**

Ball not secured against rotating. Special types on request.


## References

Thread lock on request, please refer to appendix - Technical Data -

#### **Further products**

 Ball-Ended Thrust Screws, headless, flatfaced ball


## **Drawing**



### **Order information**

Dimensions d <sub>1</sub>				ws	Load capacity for static load	ă	Art. No.
 [mm]				[mm]	max. [kN]	[g]	
flat-faced ball, bearing surface plain, for straight shanks DIN 1835 E							
M20 x 2	20	10.7	12	10	60	32	22720.0692

## **Application example**



Erwin Halder KG

www.halder.com Page 1 of 2

Published on: 3.2.2024

## Compliance

## RoHS compliant

Contains lead - compliant according to exceptions 6a / 6b / 6c.

## Contains SVHC substances >0,1% w/w

Contains lead - SVHC list [REACH] as of 23.01.2024.

### **Contains Proposition 65 substances**



Lead can cause cancer and reproductive harm from exposure https://www.P65Warnings.ca.gov/

#### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Erwin Halder KG

www.halder.com Page 2 of 2

Published on: 3.2.2024