

Spring Plungers • with ball and internal hexagon
22030.0264



Product Description

Spring plungers can be used for locating or for applying pressure, as a detent or for ejection.

Material

- Body**
- Stainless steel 1.4305
- Ball**
- Stainless steel, hardened
- Spring**
- Stainless steel

Characteristic

Heavy spring load: marked with two lines



Standard spring load



Heavy spring load

More information


Notes

Special types on request.
Spring plungers are specially tested for spring range and forces.



References

Thread lock on request, please refer to appendix - Technical Data -
Calculation of indexing resistance, please refer to appendix - Technical Data -

Drawing



Order information

Dimensions			WS	Stroke s	Spring load ¹⁾		 max.	 [g]	Art. No.
d ₁	d ₂	l			F ₁ ~	F ₂ ~	[°C]		
[mm]			[mm]	[mm]	[N]		[°C]	[g]	
stainless steel, heavy spring load									
M24	15	48	12	5.5	127	237	250	106	22030.0264

¹⁾ statistical average value

Application example



Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.