# **Centering Clamping Elements** • with clamping balls

23340.0226



# **Product Description**

To be used for accurate centering and clamping of workpieces with locating hole on which light spherical marks are acceptable. Exact self-centering with a precision of ±0,025 mm. The clamping balls frictionally center and hold workpieces with raw or pre-machined surfaces down to the bearing points. Large adjustment stroke and a small building height are a feature of this center clamping element.

Mounting from either top or bottom.

#### Material

#### **Body**

· Tool steel, hardened, blackened

# **Spring**

· Stainless steel

#### Clamping balls

· Stainless steel 1.4112, hardened and ground

#### **Assembly**

Assembly instruction for mounting from above: Remove clamping plate and screw. Screw in threaded pin from below, and tighten from above using female WS<sub>2</sub>.


Further or detailed information can be found in the assembly and operating instructions.

#### More information

#### **Further products**

- · Centering Clamping Elements, with clamping segments
- Centering Clamping Elements, with clamping segments, operation from the bottom
- Centering Clamping Elements, with clamping balls, operation from the bottom

# **Drawing**



Erwin Halder KG


#### **Order information**

|                | Dimensions     |                |   |   |                |                |                |                |                |                |                |         |   | NumberStroke |     | ws (            |                 | ClampingTightening |        |       | Location hole  |                |                |                |                |      | E   | Art. No.   |
|----------------|----------------|----------------|---|---|----------------|----------------|----------------|----------------|----------------|----------------|----------------|---------|---|--------------|-----|-----------------|-----------------|--------------------|--------|-------|----------------|----------------|----------------|----------------|----------------|------|-----|------------|
| d <sub>1</sub> | d <sub>1</sub> | d <sub>2</sub> | d | 3 | d <sub>4</sub> | h <sub>1</sub> | h <sub>2</sub> | h <sub>3</sub> | h <sub>4</sub> | h <sub>5</sub> | I <sub>1</sub> | Ball    | t | of balls     | s   | WS <sub>1</sub> | WS <sub>2</sub> | force              | torque | $D_1$ | D <sub>2</sub> | D <sub>3</sub> | D <sub>4</sub> | H <sub>1</sub> | H <sub>2</sub> | -1 " | - 1 |            |
| min.           | max            | .   f7         |   | - | +0.3           | -1             |                |                |                | -2             | ±0.10          | liamete |   | n            |     |                 |                 | F                  | max.   | H7    |                |                |                |                | +0. <b>±</b> ( | ).   |     |            |
|                |                |                |   |   |                |                |                |                |                |                |                |         |   |              |     |                 |                 | max.               |        |       |                |                |                |                |                |      |     |            |
|                | [mm]           |                |   |   |                |                |                |                |                |                |                |         |   | [mm]         | [m  | m]              | [kN]            | [Nm]               | [mm]   |       |                |                | [              | g]             |                |      |     |            |
| 26.5           | 30.5           | 20             | M | 6 | 3              | 19.8           | 14.1           | 13             | 6              | 28.8           | 7              | 4       | 8 | 3            | 2.3 | 5               | 6               | 5                  | 17     | 20    | 3              | 6              | M6             | 3.5            | 6              | 7 9  | 93  | 23340.0226 |



www.halder.com Page 1 of 2 Published on: 22.2.2024

# **Application example**



# Compliance

# **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

# Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

#### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

# **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



www.halder.com Page 2 of 2
Published on: 22.2.2024