

**Multi-Vices MS 125**

EH 1700.



**MULTI-VICE – MECHANICAL  
VERSION MS 125-S/M/L**

**SCOPE OF APPLICATION**

- Can be applied horizontally or vertically - therefore suitable for vertical and horizontal CNC milling machines
- Conventional clamping, gripper clamping or pull-down clamping are all possible
- MS 125-S – ideal for use on five-axis machining centres
- Clamping unmachined parts, saw-cut or flame-cut material by penetration of hardened, replaceable gripper elements into the workpiece
- With the support jaws, unmachined parts in highly varied materials, or with complex geometries, can be clamped securely and economically

**PRODUCT FEATURES**

- High versatility: the modular clamping system combines practically all the possibilities of our tried-and-tested models
- High-pressure spindle with power intensification - clamping force does not slacken
- Enlarged clamping span for secure clamping of unmachined parts
- Lost clamping margin 8 mm with pull-down clamping, 3 mm with gripp clamping
- Clamping with torque wrench (max. 30 Nm) - this makes it possible to work above the table with an unfavourable clamping arrangement on the tool



You will find details and your contact persons under:



[www.halder.com/  
Multi-Vices](http://www.halder.com/Multi-Vices)